








REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	/
A1	N/A		图面升级整理图面	2025.04.26





X05ADHWW6SBW1

1:Au=1U"
3:Au=3U"
4:Au=6U"
5:Au=15U"
6:Au=30U"



DIMENSIONS OF PC BOARD HOLES
TOLERANCE:±0.05(PRINTED-SIDED VIEW)



MATERIAL 材料:
HOUSING 外壳: LCP,UL94V-0,BLACK.
TERMINAL 端子: PHOSPHOR BRONZE , ϕ =0.46MM,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:
DURABILITY 耐用性: 750 CYCLES MIN.600 times /H
INSERTION FORCE 插入力: 2.2KG.F MAX
Withdrawal Force 拔出力: 44N Max.
OPERATING TEMPERATURE 工作温度: -25°C~+70°C.
STORAGE TEMPERATURE 储存温度: -0°C~+70°C.

ELECTRICAL 电动:
VOLTAGE 电压:12 V
CURRENT RATING 额定电流:0.5A AC
DIELECTRIC STRENGTH 介电强度:500V AC ,2mA shall be applied between adjacent contacts for 1 minute at 50 or 60 Hz.
INSULATION RESISTANCE 绝缘电阻:500 MEGA OHMS MIN.INITIAL
AFTER 500V DC FOR 1 MINUTE
CONTACT RESISTANCE 接触电阻:100m Ω or less

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: RJ JACK
CHECKED		UNIT: mm/in	PART NO.: X05ADHWW6SBW1
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1