







R1



R2



PCB LAYOUT (R1)



PCB LAYOUT (R2)

Specifications:
规格:
Voltage rating: 250V AC/DC
额定电压: 250V AC/DC
Current rating: 1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage: 300V AC/minute
耐受电压: 300V AC/分钟
Temperature range: -40°C ~ +105°C
温度范围: -40°C ~ +105°C
Insulation resistance: ≥ 500MΩ
绝缘电阻: ≥ 500MΩ
Contact resistance: ≤ 20mΩ
接触电阻: ≤ 20mΩ
Material: PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category: 1U"Gold
镀层: 1U"Gold
Reflow soldering temperature: 260 ± 5°C, 10S
回流焊温度: 260 ± 5°C, 10S

X1311 F V S - 22 - C43 D35 R1
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No
2. Category: F-Female
3. Welding Board Angle: V-Straight 180°
4. Welding Way: S-SMT
5. Row No. Pin No: XX-01~40Pin
6. Plastic Height: C=4.3mm
7. Pin pitch: D=3.5mm
8. Type: R1 ; R2

X1311FVS-22-C43D35R1	PA6T	Brass	X1311W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector		
DWN		VIEW: 	PART NO.: X1311FVS-22-C43D35R1		
CHKD		UNIT: mm/in	DWG NO.: X-X1311FVS-22-C43D35R1		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0