

1


2

3



4

A

A



STRADDLE MOUNT
WITH MOUNTING EAR TYPE



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.:
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/3	A1

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.17	阿树

NOTES 注释:

1. MATERIAL材料:

1.1 HOUSING外壳: THERMOPLASTIC, HIGH TEMP.,UL94V-0;
COLOR: BLACK.

1.2 CONTACTS触点: COPPER ALLOY.

2. FINISH饰面:

2.1 CONTACT触点:

SELECTIVE GOLD PLATING ON CONTACT AREA.
100 μ" MIN. MATTE TIN PLATING ON SOLDER TAILS,
50 μ" MIN. NICKEL UNDERPLATING OVERALL.

PART NO.:

X3126 W S-164-9T V15
① ② ③ ④ ⑤ ⑥

①Series No

②Category:W-Wafer

③Welding Board Angle : Straddle



④No.of Pins: 36~164 Pin

⑤lastic material: PA9T /PA46 UL94V-0

⑥Contact Plating:V01-Gold Flash

V15-Gold 15u"

V30-Gold 30u"



DIMENSIONS					
POSITION	A±0.20	B±0.15	C±0.20	D±0.25	E±0.30
36	6	7.65	12.30	25.00	34.8
64	20	21.65	26.30	39.00	48.8
98	37	38.65	43.30	56.00	65.8
164	70	71.65	76.30	89.00	98.8

D

D



1

2

3


4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.17	阿树




RECOMMENDED OF PCB DIMENSIONS
TOLERANCE: ±0.05

I/O PANEL DIRECTION
PRIMARY (COMPONENT) SIDE



I/O PANEL DIRECTION
SECONDARY (SOLDER) SIDE



SCALE 2:1





DIMENSIONS				
POSITION	A	C	F	G
36	6.00	12.30	8.15	B PIN#17
64	20.00	26.30	22.15	B PIN#31
98	37.00	43.30	39.15	B PIN#48
164	70.00	76.30	72.15	B PIN#81

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	/	
CHECKED		UNIT:	mm/in	PART NO.:	X3126WS-164-9TV15	
APPROVED		SIZE:	A4	DWG NO.:	X-X3126WS-164-9TV15	
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	2/3	A1

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.17	阿树



DIMENSIONS	
POSITION	H
36	20.4
64	34.4
98	51.4
164	84.4

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: /
CHECKED		UNIT: mm/in	PART NO.: X3126WS-164-9TV15
APPROVED		SIZE: A4	DWG NO.: X-X3126WS-164-9TV15

SCALE	PAGE	REVISION
N/A	3/3	A1