

1



2

3


4

REVISIONS



REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.06	阿树



SPECIFICATION
Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.25mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃



CIRCUIT DIAGRAM



PCB LAYOUT

PAPT NO	TS-1188A-B-A
Operating Force	B:160gf C:260gf
Height	H:A:3.55 B:4.3 C:5.0

⑤	Terminal	4	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	Lcp	
②	Cover	1	Brass	Plating Nickel
①	Keystake	1	Lcp	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TS-1188A-B-A
APPROVED		SIZE:	A4	DWG NO.:	TS-1188A-B-A
			SCALE	PAGE	REVISION
			N/A	1/1	A1

1

2

3

4