

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 甚


规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
2.接触电阻 Contact resistance:≤30 mΩ
3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
4.电气寿命 Electronics life:>10000 cycles
5.操作力 Operation force:500±150gf
6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:


SS-X 03 23 P G-4 N 5 W W
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
③ Current Rating: 03-3A;
④ Switch Circuit:23-2P3T;
⑤ P: Welding plates;
⑥ Handle Shape: G-Camber handle;
⑦ Handle Height: 3~15mm;
⑧ Enclosure Shape:N-Square enclosure;
⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
⑩ Handle Colour:
B-Black; W-White; R-Red
⑪ Housing Colour:
B-Black; W-White; R-Red



产品字码标识

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 甚	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	SLIDE SWITCH
APPROVED		SIZE: A4	PART NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED		SS-0323PG-4N5WW	
		DWG NO.:	
		X-SS-0323PG-4N5WW	
		SCALE	PAGE
		N/A	1/1
		REVISION	
			A0

