





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.17	阿树



Specifications:
规格:
Voltage rating: 30V AC/DC
额定电压: 30V AC/DC
Current rating: 3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage: 100V AC/minute
耐受电压: 100V AC/分钟
Temperature range: -35°C - +85°C
温度范围: -35°C - +85°C
Insulation resistance: 50MΩ min
绝缘电阻: 50MΩ Min
Contact resistance: 90mΩ Max
接触电阻: 90mΩ Max



PART NO.:

X3500 W V S-24 A-LP V01
 (1) (2) (3) (4) (5) (6) (7) (8)

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-10Pin-60Pin
⑥High:A=0.6mm
Mating Height 0.7mm
⑦Material:LP-LCP UL 94V-0 Black
⑧Plating:V01-Gold Flash;

Poles	A	B	C
10	3.57	2.26	1.40
24	6.02	4.71	3.85
30	7.07	5.76	4.90
34	7.77	6.46	5.60
38	8.47	7.16	6.30
40	8.82	7.51	6.65
50	10.57	9.26	8.40
60	12.32	11.01	10.15

X3500WVS-24A-LPV01	LCP UL 94V-0	Copper Alloy	X3500WVS
PART NO	Material	Material(Pin)	Suitable XH Female

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XK13 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 0.35mm BTB Style Connector
CHECKED		UNIT: mm/in	PART NO.: X3500WVS-24A-LPV01
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1