




LEFT SIDE VIEW





FRONT VIEW




BOTTOM VIEW



RIGHT SIDE VIEW

RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE


TOP VIEW



BACK VIEW

ELECTRICAL电气特性:

1. Turn ratio 匝数比:1~2:J1~J2=1CT:1CT(±2%)
3~6:J3~J6=1CT:1CT(±2%)
2. OCL 已占搭载量:350uH Min.at 100KHz 100mV 8mA DC.
3. Insertion Loss 插入损耗: -1.0 dB Max 1~100MHz
4. Return loss 回程损耗: -20dB Min 1~10MHz
-16dB Min 10~30MHz
-12dB Min 30~60MHz
-10dB Min 60~80MHz
5. Cross talk 声道串扰: -40dB Min 1~30MHz;
-35dB Min 30~60MHz;
-30dB Min 60~100MHz;
6. CMR 共模抑制: -30dB Min 1~100MHz;
7. Hi-Pot 耐压测试: 1500V AC & 2250V DC 6S
1mA PRI TO SEC



XKB Connectivity

MATERIAL 材料:

HOUSING 外壳: PBT,UL94V-0,BLACK.

TERMINALS BRACKET 端子支架: PBT,UL94V-0,BLACK.

SHIELD 保护物: C2680.T=0.20MM,NICKEL PLATING ON ALL AREA.

TERMINAL 端子: PHOSPHOR BRONZE C5210, T=0.35MM,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN.

MATING FORCE 配合力: 23N MAX.

OPERATING TEMPERATURE 工作温度: -40°C~+85°C.

STORAGE TEMPERATURE 儲存溫度: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH "*"

东星坤科技股份有限公司							DSND		SCALE: N/A	MODEL TYPE: RJ JACK		
ΔX					ANGLAR	±5°	XK13	DWN		VIEW: 	PART NO.:	
ΔX					L ≤ 4	±0.2		CHKD		UNIT: mm/in	DWG NO.:	
ΔX					4<L≤ 16	±0.3		APPD		SIZE: A4	X01AB002GWDD	
MARK					16<L≤ 63	±0.4						
					L > 63	±0.5						
REVISIONS										WEIGHT	SHEET	REVISIOI
UNSPECIFIED TOLERANCES							XKB INDUSTRIAL PRECISION CO.,LIMITED					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn										1/1 A0		