


With CAP

Without CAP

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0


材质: PA6T UL94V-0

Plating Category:1U"Gold


镀层: 1U"Gold

Reflow soldering temperature:260±5℃, 10S


回流焊温度: 260±5℃, 10S




Type R1



Type R2



P.C.B LAYOUT(R1 Type)



P.C.B LAYOUT(R2 Type)

X6511 F V S - 06- C85 D48 R1
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX Pin
- 6.Plastic high:C=8.5mm
- 7.Pin Pitch:D=4.8mm
- 8.Type:X-R1 ; R2

X6511FVS-06-C85D48R1	PA6T	Brass	X6511W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
ΔX					
MARK					
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.54mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X6511FVS-06-C85D48R1
APPD	SIZE: A4	DWG NO.: X-X6511FVS-06-C85D48R1
		WEIGHT
		SHEET
		REVISION
		1/1
		A0