



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing: $\leq 30m\Omega$


X2012 H- 02-N0

① ② ③ ④

- ① SeriesNumber
- ② Category : H-HSG
- ③ Row No.Pin No:xx-02-15P
- ④ Material:N0-PA66 UL 94V-0



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.20	5.10	10	18.00	22.20	21.10
03	4.00	8.20	7.10	11	20.00	24.20	23.10
04	6.00	10.20	9.10	12	22.00	26.20	25.10
05	8.00	12.20	11.10	13	24.00	28.20	27.10
06	10.00	14.20	13.10	14	26.00	30.20	29.10
07	12.00	16.20	15.10	15	28.00	32.20	31.10
08	14.00	18.20	17.10	16			
09	16.00	20.20	19.10				



X2012H-02-N0	PA66 UL 94V-0	X2012T	X2012W
PARY N0	Matrial	Suitable XKB Terminal	Suitable XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors			
Δx					ANGULAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2012H-02-N0			
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2012H-02-N0			
Δx					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4				
Δx					16<L ≤ 63	±0.4									
MARK	DESCRIPTION				DATE	REVISED	APPROVED	L > 63		±0.5					
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED			
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT 1.0g			
												SHEET 1/1			
												REVISION A0			