










Shipping Arrangement:50 sets per strip
Shipped in carton box



Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:2A AC/DC
额定电流: 2A AC/DC
Withstanding voltage:1200V AC/minute
耐受电压: 1200V AC/分钟
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max

PART NO.:
X25071 H I-03 E 12-PT SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:H-HSG
- ③Category:I-Punctured type
- ④Row No.Pin No:XX-02~17 Pin
- ⑤Appearance type:E Type
- ⑥pacer bar:For example12-Keying between pin 1 and pin 2
23-Keying between pin 2 and pin 3...When the pin number is above 10,use the letters A ,B C...A for 10,B for 11...
- Blank-No Keying
- ⑦Material:PT-PBT ;N0-PA66 UL 94V-0
- ⑧Platig:SN-Plated Tin; V01-Gold Flash;
V03-Gold 3u; V15-Gold 15u;V30-Gold 30u



Poles	Dimensions(mm)		Spacer bar	C		D
	A	B	00	/	/	
02	7.40	2.50	12	3.70	1.25	
03	9.90	5.00	23	6.20	3.75	
04	12.40	7.50	34	8.70	6.25	
05	14.90	10.00	45	11.20	8.75	
06	17.40	12.50	56	13.70	11.25	
07	19.90	15.00	67	16.20	13.75	
08	22.40	17.50	78	18.70	16.25	
09	24.90	20.00	89	21.20	18.75	
10	27.40	22.50	9A	23.70	21.25	
11	29.90	25.00	AB	26.20	23.75	
12	32.40	27.50	BC	28.70	26.25	
13	34.90	30.00	CD	31.20	28.75	
14	37.40	32.50	DE	33.70	31.25	
15	39.90	35.00	EF	36.20	33.75	
16	42.40	37.50	FG	38.70	36.25	
17	44.90	40.00	GH	41.20	38.75	

X25071HI-03E12-PTSN	AWG24~22	Phosphor
PART NO	Wire Range	Material(Pin)

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
2.50mm Pitch Rast Connector
PART NO.:
X25071HI-03E12-PTSN
DWG NO.: