


| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE |            |        |
| A1        | N/A     |          | 图面升级整理图面        | 2024.08.21 | 阿树     |



Specifications:  
规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:7A AC/DC  
额定电流: 7A AC/DC  
Withstanding voltage:1500V AC/minute  
耐受电压: 1500V AC/分钟  
Temperature range:-40℃-+125℃  
温度范围: -40℃-+125℃  
Insulation resistance:1000MΩ min  
绝缘电阻: 1000MΩ Min  
Contact resistance:10mΩ Max  
接触电阻: 10mΩ Max

X9396 T-B 01-U  
① ② ③ ④ ⑤

- 1.Series No
- 2.Category:T-Terminal
- 3.Material:B-Beass
- 4.Plating:SN-Plated Tin  
V01-Gold 1u''
- 5.Special No:U-upgraded version

SECTION: A-A  
SCALE:1:1

SECTION: B-B  
SCALE:1:1

|               |          |            |                      |
|---------------|----------|------------|----------------------|
| X9396T-BV01-U | Brass    | AWG#24~16  | X9396H               |
| PART NO       | Material | Wire Range | Suitable XKB Housing |

|                        |       |
|------------------------|-------|
| ANGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |    |             |             |                                             |
|----------|----|-------------|-------------|---------------------------------------------|
| DESIGN   | 阿树 | VIEWS       | UNIT: mm/in | MODEL TYPE:<br>3.96mm Crimp Style Connector |
| CHECKED  |    | UNIT: mm/in |             | PART NO.:<br>X9396T-BV01-U                  |
| APPROVED |    | SIZE: A4    |             | DWG NO.:                                    |