










Recommended Panel Cut - Out
Thick:1.27mm Min/1.57mm Max

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/ 分钟

Temperature range:-40 ℃ -+105℃

温度范围: -40℃ -+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

X3025 H F - 2x06 WS - N0

① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:H-HSG

3.Category:F-Female Housing

4.Row No.Pin No:XX-2x01~2x12P

5.Special No:WS-With Base

6.Material:N0-PA66 94V-0

Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2x01	/	/	/	/	2x07	35.30	18.00	29.85	35.85
2x02	20.30	3.00	14.85	20.85	2x08	38.30	21.00	32.85	38.85
2x03	23.30	6.00	17.85	23.85	2x09	41.30	24.00	35.85	41.85
2x04	26.30	9.00	20.85	26.85	2x10	44.30	27.00	38.85	44.85
2x05	29.30	12.00	23.85	29.85	2x11	47.30	30.00	41.85	47.85
2x06	32.30	15.00	26.85	32.85	2x12	50.30	33.00	44.85	50.85

X3025HF-2x06WS-N0	PA66	X3025HM	X3025TM
PART NO	Material	Suitable XKB Housing	Suitable XKB Terminal

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 3.0mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X3025HF-2x06WS-N0		
CHKD		UNIT: mm/in	DWG NO.: X-X3025HF-2x06WS-N0		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0