




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		模具变更, 图面升级整理图面	2025.10.17	阿树





SCHEMATIC



PCB LAYOUT
BOTTOM VIEW

SS22D03L5

L(MM)
2 ~ 10



RATING	0.3A 50V DC
CIRCUIT	2P2T
CONTACT RESISTANCE	100MΩ MAX
TRAVEL	2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS22D03L5
APPROVED		SIZE:	A4	DWG NO.:	