



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.04	阿树





■SPECIFICATIONS

- Voltage rating:100V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:500V AC/minute
- Temperature range:−40°C~+125°C
- Insulation resistance:≥500MΩ
- Contact resistance:≤20mΩ

PART NO.:

X1502 H-16-N0
① ② ③ ④

- ①Series No
②Category:H-Housing
③Row No.Pin No:XX-02~15Pin
④Material:N0-PA66 UL 94V-0



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	1.50	4.50	09	12.00	15.00
03	3.00	6.00	10	13.50	16.50
04	4.50	7.50	11	15.00	18.00
05	6.00	9.00	12	16.50	19.50
06	7.50	10.50	13	18.00	21.00
07	9.00	12.00	14	19.50	22.50
08	10.50	13.50	15	21.00	24.00

X1502H-16-N0		PA66	X1502W	X1502T
PART NO		Material	Suitable XKB Wafer	Suitable XKB Terminal
DESIGN	阿树	VIEW:	MODEL TYPE: 1.50mm Crimp Style Connectors	
CHECKED		UNIT: mm/in	PART NO.: X1502H-16-N0	
APPROVED		SIZE: A4	DWG NO.:	

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

