





Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M \Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing : $\leq 30m\Omega$

X2012 W R-10- N0 SN

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : R-Sright 90°
- ④ Row No.-Pin No.: XX-02P~15P
- ⑤ Material : N0-PA66 94V-0
- ⑥ Plating Category: Sn-Bright Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	5.20	10	18.00	22.00	21.20
03	4.00	8.00	7.20	11	20.00	24.00	23.20
04	6.00	10.00	9.20	12	22.00	26.00	25.20
05	8.00	12.00	11.20	13	24.00	28.00	27.20
06	10.0	14.00	13.20	14	26.00	30.00	29.20
07	12.0	16.00	15.20	15	28.00	32.00	31.20
08	14.0	18.00	17.20				
09	16.0	20.00	19.20				

X2012WR-10-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X2012H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors		
Δx					ANGULAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X2012WR-10-N0SN		
Δx					$4 < L \leq 16$	± 0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X2012WR-10-N0SN		
Δx					$16 < L \leq 63$	± 0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED						$L > 63$	± 0.5	
REVISIONS												XKB INDUSTRIAL PRECISION CO.,LIMITED		
												WEIGHT		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												1.0g		
												SHEET		
												1/1		
												REVISION		
												A0		