



Specifications:
Voltage rating:250V AC/DC
Current rating:2A AC/DC
Withstanding voltage:800V AC/minute
Temperature range:-40℃~+85℃
Insulation resistance:≥1000MΩ
Contact resistance:≤20mΩ





X2016 H M - 09 - N0

① ② ③ ④ ⑤

1.Series No
2.Category:H-Housing
3.M-Male
4.Row No.Pin No:XX-02~16P
5.Material:N0-PA66 UL 94V-0

POLES	A	B	C
2	2.00	4.60	5.80
3	4.00	6.60	7.80
4	6.00	8.60	9.80
5	8.00	10.60	11.80
6	10.00	12.60	13.80
7	12.00	14.60	15.80
8	14.00	16.60	17.80
9	16.00	18.60	19.80
10	18.00	20.60	21.80
11	20.00	22.60	23.80
12	22.00	24.60	25.80
13	24.00	26.60	27.80
14	26.00	28.60	29.80
15	28.00	30.60	31.80
16	30.00	32.60	33.80



X2016HM-09-N0	PA66 UL 94V-0	X2016TF	X2016W X2016HF
PARY N0	Matrial	Suitable XKB Terminal	Suitable XKB Wafer or Housing

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors		
DWN		VIEW: 	PART NO.: X2016HM-09-N0		
CHKD		UNIT: mm/in	DWG NO.: X-X2016HM-09-N0		
APPD		SIZE: A4			
PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxb.com www.helloxb.cn www.xk-da.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED