




D

	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.04.01	阿樹
/	N/A		/	/	/



- SPECIFICATIONS
- Voltage rating:600V AC/DC
 - Current rating:9A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-45°C+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤20mΩ



PART NO.:

X9357 H M-2X03 N2
① ② ③ ④ ⑤

- ①Series No
②Category:H-HSG
③Welding Board Angle:M-Male HGS
④Row No.-Pin No.:2X11P
⑤Material:N2-PA66 94V-2 White

X9357HM-2x03-N2	PA66	X9357W-A	X9357HF
PART NO	Material	Suitable XBK Wafer	Suitable XBK Housing

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERANCE



DESIGN	阿树	VIEW: 	MODEL TYPE: 4.20 mm Crimp Style Connector		
CHECKED		UNIT: mm/in	PART NO.: X9357HM-2x03-N2		
APPROVED		SIZE: A4	DWG NO.: X-X9357HM-2x03-N2		
PRECISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A0

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0