



A



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.07.27	阿树

PART NO.:

X9357 H F-05 I N2 XX
① ② ③ ④ ⑤ ⑥ ⑦

Specifications:

Voltage rating:600V AC/DC

Current rating:9A AC/DC

Withstanding voltage:1500V AC/minute

Temperature range:-45℃-+125℃

Insulation resistance:≥1000MΩ



Contact resistance:≤10mΩ

After environmental testing:≤20mΩ

- ① Series No
② Category:H-HSG
③ Welding Board Angle:F-Female
④ Row No-Pin No: XX-02P~12P
⑤ Plug the Pin & special No:
I-Without the Wing; G-With Ears
⑥ Material:N0-PA66 UL94V-0;N2-PA66 94V-2
⑦ Color: Blank-Natural Color

B

C



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	4.20	9.80	08	29.40	35.00
03	8.40	14.00	09	33.60	39.20
04	12.60	18.20	10	37.80	43.40
05	16.80	22.40	11	42.00	47.60
06	21.00	26.60	12	46.20	51.80
07	25.20	30.80			

X9357HF-05G-N2	Nylon 66 94v-2	X9357TM	X9357M Or X9357H	With Ears
X9357HF-05I-N2				Without Ears
X9357HF-05G-N0	Nylon 66 94v-0			With Ears
X9357HF-05I-N0				Without Ears
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal	Note

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 4.20 mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X9357HF-05I-N2
APPROVED		SIZE:	A4	DWG NO.: X-X9357HF-05I-N2

A

B

C

D