

1

2

3

4

A

A

B

B

C

C

D

D

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 葚




规格 Specification:

- 额定值 Rating:3A 125/250VAC
- 接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 电气寿命 Electronics life: > 10000 cycles
- 操作力 Operation force: $500\pm 150\text{gf}$
- 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 24 P G-10 N 1 B B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
③ Current Rating: 03-3A;
④ Switch Circuit:24-2P4T;
⑤ P: Welding plates;
⑥ Handle Shape: G-Camber handle;
⑦ Handle Height: 3~15mm;
⑧ Enclosure Shape:N-Square enclosure;
⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
⑩ Handle Colour:
B-Black; W-White; R-Red
⑪ Housing Colour:
B-Black; W-White; R-Red



产品字码标识

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 葚	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS-0324PG-10N1BB
APPROVED		SIZE:	A4	DWG NO.:	X-SS-0324PG-10N1BB
		SCALE		PAGE	1/1
				REVISION	A0

25.00 [0.984]

10.50 [0.413]

5.50 [0.217]

4.00 [0.157] Travel

8.50 [0.335]

1.35 [0.053]

4.50 [0.177]

18.00 [0.709]

2.00 [0.079]

4.50 [0.177]

6.70 [0.264]

0.80 [0.031]

PCB LAYOUT

1

2

3

4