




Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating: 2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage:1500V AC/minute

耐压电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

Insulation resistance: $\geq 1000\text{M}\Omega$

绝缘电阻: $\geq 1000\text{M}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

接触电阻:≤20mΩ

Linetype:AWG#22 AWG#24 AWG#26 AWG#28

X9254 H IR - 02 - N0

① ② ③ ④ ⑤

①Series No.

②Category: H-HSG

③Welding Board Angle: I-HSG+Hardware R-Right Angle 90°

④Row No.-Pin No.: XX-02P~30P

⑤Material: N0-PA66 94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.20	10	22.86	25.52
3	5.08	7.72	11	25.40	28.06
4	7.62	10.28	12	27.94	30.60
5	10.16	12.82	30	73.66	76.32
6	12.70	15.36			
7	15.24	17.90			
8	17.78	20.44			
9	20.32	2.98			

X9254HIR-02-N0	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9254W
PART N0	Material	Material(Pin)	Finish(Terminal)	Wire Range

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54mm IDC Style Connectors			
ΔX					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X9254HIR-02-N0			
ΔX					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9254HIR-02-N0			
ΔX					4<L ≤ 16	±0.3	APPD		DATE		SIZE: A4				
ΔX					16<L ≤ 63	±0.4									
MARK	DESCRIPTION				DATE	REVISED	APPROVED	L > 63		±0.5					
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED			
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												WEIGHT 1.0g			
												SHEET 1/1			
												REVISION A0			