





X1004-H-2x10-N0          

①                      ②                      ③                      ④

- | PIN  | DIM.(MM) |       |
|------|----------|-------|
|      | A        | B     |
| 2X08 | 7.00     | 9.70  |
| 2X10 | 9.00     | 11.70 |
| 2X15 | 14.00    | 16.70 |
| 2X16 | 15.00    | 17.70 |
| 2X20 | 19.00    | 21.70 |
| 2X25 | 24.00    | 26.70 |

|                  |             |  |  |      |           |          |                        |      |                                      |      |                                                                                             |                                     |                                               |              |                |  |
|------------------|-------------|--|--|------|-----------|----------|------------------------|------|--------------------------------------|------|---------------------------------------------------------------------------------------------|-------------------------------------|-----------------------------------------------|--------------|----------------|--|
|                  |             |  |  |      |           |          | XKB                    | DSND |                                      | DATE |                                                                                             | SCALE: N/A                          | MODEL TYPE:<br>2.54 mm Crimp Style Connectors |              |                |  |
|                  |             |  |  | XKB  | ANGLAR    | ±5°      | DWN                    |      | DATE                                 |      | VIEW:  | PART NO.:<br><b>X1004H-2x10-N0</b>  |                                               |              |                |  |
| ΔX               |             |  |  |      | L ≤ 4     | ±0.2     | CHKD                   |      | DATE                                 |      | UNIT: mm/in                                                                                 | DWG NO.:<br><b>X-X1004H-2x10-N0</b> |                                               |              |                |  |
| ΔX               |             |  |  |      | 4<L ≤ 16  | ±0.3     | APPD                   |      | DATE                                 |      | SIZE: A4                                                                                    |                                     |                                               |              |                |  |
| ΔX               |             |  |  |      | 16<L ≤ 63 | ±0.4     |                        |      |                                      |      |                                                                                             |                                     |                                               |              |                |  |
| MARK             | DESCRIPTION |  |  | DATE | REVISED   | APPROVED |                        |      |                                      |      |                                                                                             |                                     |                                               |              |                |  |
| REVISIONS        |             |  |  |      |           |          | UNSPECIFIED TOLERANCES |      | XKB INDUSTRIAL PRECISION CO.,LIMITED |      |                                                                                             |                                     | WEIGHT<br>1.0g                                | SHEET<br>1/1 | REVISION<br>A0 |  |
| www.helloxkb.com |             |  |  |      |           |          |                        |      |                                      |      |                                                                                             |                                     |                                               |              |                |  |