

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+105℃

温度范围: -25℃~+105℃

Insulation resistance:1000MΩ min


绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2513 W R - 2x05 A - LP SN
① ② ③ ④ ⑤ ⑥ ⑦

	2x02	2x03	2x04	2x05
A Key Color:Black				
B Key Color:Natural				
	2x06	2x07	2x08	
A Key Color:Black				
B Key Color:Natural				



Recommended P.C.B hloe dimension
Recommended P.C.B thickness 1.6~2.4mm

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Range:R-Stright 90°
- 4.Row No.Pin No:2xXX-2x02~2x08 Pin
- 5.Special No: A:A Key ; B:B Key
- 6.Material:LP-LCP UL94V-0
- 7.Plating:SN-Tin plated

Circuit	DIM. A	DIM. B
N(N=4~16)	1.25 x N - 2.5	1.25 x N + 0.94

X2513WR-2x05A-LPSN	LCP	Copper Alloy	X2513H
X2513WR-2x05B-LPSN			
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector	
DWN	VIEW:	PART NO.: X2513WR-2x05A-LPSN	
CHKD	UNIT: mm/in	DWG NO.: X-X2513WR-2x05A-LPSN	
APPD	SIZE: A4	WEIGHT	SHEET
		1/1	REVISION A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED