





规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 3.绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 4.电气寿命 Electronics life: $> 10000\text{ cycles}$
- 5.操作力 Operation force: $500\pm 150\text{ gf}$
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:


$$\frac{SS-X}{(1)} \quad \frac{03}{(2)} \quad \frac{22}{(3)} \quad \frac{S}{(4)} \quad \frac{G-4}{(5)} \quad \frac{R}{(6)} \quad \frac{4}{(7)} \quad \frac{B}{(8)} \quad \frac{B}{(9)} \quad \frac{B}{(10)} \quad \frac{B}{(11)}$$

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A—Metal case;
BLANK—Plastic case;
- ③ Current Rating: 03—3A;
- ④ Switch Circuit: 22—2P2T;
- ⑤ S: Wire bonding;
- ⑥ Handle Shape: G—Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: R—Locking rings enclosure;
- ⑨ Terminal specs:
1: TYPE—1; 2: TYPE—2; 3: TYPE—3;
4: TYPE—4; 5: TYPE—5;
- ⑩ Handle Colour:
B—Black; W—White; R—Red
- ⑪ Housing Colour:
B—Black; W—White; R—Red



产品字码标识

ANGLAR	$\pm 5^{\circ}$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 荳	VIEW:		MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in		PART NO.: SS-0322SG-4R4BB
APPROVED		SIZE: A4		DWG NO.: X-SS-0322SG-4R4BB
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1 / 1
			REVISION Δ0	