





- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 20\text{m}\Omega$
- After environmental testing : $\leq 30\text{m}\Omega$

X2012 W R-06- N0 SN

① ② ③ ④ ⑤ ⑥

① Series No.

② Category : W-WAFER

③ Wedding Board Angle : R-Straight 90°

④ Row No.-Pin No.: XX-02P~15P

⑤ Material : N0-PA66 94V-0

⑥ Plating Category: Sn-Bright Tin Plating

X2012WR-06-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X2012H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors		
ΔX					ANGULAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.:		
ΔX					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	X2012WR-06-N0SN		
ΔX					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4	DWG NO.:		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$16 < L \leq 63$	± 0.4						X2012WR-06-N0SN		
					$L > 63$	± 0.5								
REVISIONS							UNSPECIFIED TOLERANCES							
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	SHEET 1/1	REVISION A0