



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图纸更正, 图面升级整理图面	2024.9.04	阿树



■ SPECIFICATIONS

- Voltage rating:100V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:500V AC/minute
- Temperature range:−40°C~+125°C
- Insulation resistance:≥500MΩ
- Contact resistance:≤20mΩ



PART NO.:

X1502 W V-13-46 V03
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No.Pin No:XX-02~20Pin
⑤Material:46-PA46 UL94V-0
⑥Planting:V03-Gold 3u"

Poles	Dimensions (mm)	
	A	B
02	1.50	4.50
03	3.00	6.00
04	4.50	7.50
05	6.00	9.00
06	7.50	10.50
07	9.00	12.00
08	10.50	13.50
09	12.00	15.00
10	13.50	16.50
11	15.00	18.00
12	16.50	19.50
13	18.00	21.00
20	20.50	31.50

X1502WV-13-46V03	PA46	Brass	X1502H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKB 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 1.50mm Crimp Style Connectors		
CHECKED		UNIT: mm/in	PART NO.: X1502WV-13-46V03		
APPROVED		SIZE: A4	DWG NO.: X-X1502WV-13-46V03		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1

MODEL TYPE: 1.50mm Crimp Style Connectors		
PART NO.: X1502WV-13-46V03		
DWG NO.: X-X1502WV-13-46V03		
SCALE N/A	PAGE 1/1	REVISION A1