







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A)X2	尺寸变更, 新增不同颜色卡位图面, 图面升级整理图面	2025.1.9	阿树




K776280WR-14-PTXXB



K776280WR-14-PTXXW



K776280WR-14-PTXXGY



K776280WR-14-PTXXBL

Current rating:7A AC/DC
额定电流: 7A AC/DC
Temperature range:-40℃~+85℃
温度范围: -40℃~+85℃

PART NO.:

K 776280 W R-14-PT SN B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①K:XKBTEK-Car Connector
- ②XKB Series No
- ③Category:W-Wafer
- ④Welding Board Range:R-Stright 90°
- ⑤Row No.Pin No:14 Pin
- ⑥Material:PT-PBT
- ⑦Palting:V01-Gold Flash ;SN-Plated Tin
- ⑧Color:X:B-Black; W-White; GY-Gray; BL-Blue

PLAYTING	COLOR	NAME
Gold Flash	Blue	K776280WR-14-PTV01BL
Gold Flash	Gray	K776280WR-14-PTV01GY
Gold Flash	White	K776280WR-14-PTV01W
Gold Flash	Black	K776280WR-14-PTV01B
Plated Tin	Blue	K776280WR-14-PTSBNB
Plated Tin	Gray	K776280WR-14-PTSNGY
Plated Tin	White	K776280WR-14-PTSBNW
Plated Tin	Black	K776280WR-14-PTSBNB

K776280WR-14-PTSBNB	PBT	Brass	K776280H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 4.0mm Automobile connector
CHECKED		UNIT: mm/in	PART NO.: K776280WR-14-PTSBNB
APPROVED		SIZE: A4	DWG NO.: X-K776280WR-14-PTSBNB

SCALE	PAGE	REVISION
N/A	1/1	A1