






Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ min

Contact resistance:20mΩ max

接触电阻: 20mΩ max

X4140 H F - 2x02 - N0

① ② ③ ④ ⑤

1.Series No

2.Category:H-Housing

3.Housing Type:F-Female Housing

4.Row No,Pin No:2xXX-2x02~2x03P

5.Material:N0-PA66 94V-0

Poles	Dimensions(mm)	
	A	B
2x02	4.14	9.80
2x03	8.28	14.00

X4140HF-2x02-N0	PA66	X4140W	X4140HM	X4140TM
PART N0	Material	Suitable XKB Wafer	Suitable XKB Housing	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 4.14mm Crimp Style Connector	
DWN		VIEW:	PART NO.: X4140HF-2x02-N0	
CHKD		UNIT: mm/in	DWG NO.: X-X4140HF-2x02-N0	
APPD		SIZE: A4		
			WEIGHT	SHEET
			1/1	A0

					ANGULAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED