





Assembly Layout

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤30mΩ

接触电阻: ≤30mΩ

After environmental testing:≤40mΩ

环境测试后: ≤40兆欧

X2011 W R S-07 A -9T SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:R-Right Angle 90°

4.Welding Way:S-SMT

5.Row No-Pin No:XX-02P~16P

6.Plug the Pin&Special N0:

A-With Located Block

7.Material:9T:PA9T UL 94V-0

8.Plating Category:SN-Bright Tin Plating

9.Color:Blank-Natural Color

poles	Dimensions(mm)				poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
2	8.00	2.00	2.70	4.75	10	24.00	18.00	15.50	20.90
3	10.00	4.00	3.20	6.75	11	26.00	20.00	15.50	22.90
4	12.00	6.00	3.50	8.90	12	28.00	22.00	15.50	24.90
5	14.00	8.00	5.50	10.90	13	30.00	24.00	15.50	26.90
6	16.00	10.00	7.50	12.90	14	32.00	26.00	15.50	28.90
7	18.00	12.00	9.50	14.90	15	34.00	28.00	15.50	30.90
8	20.00	14.00	11.50	16.90	16	36.00	30.00	15.50	32.90
9	22.00	16.00	13.50	18.90					

X2011WRS-07A-9TSN	PA9T UL 94V-0	Brass	Phosphor Bronze	Tin-Plated	X2011H-A
PART NO	Material	Material(pin)	Material(Solder Tab)	Finish(Pin and Solder tab)	Suitable XKB Housing

Wire to board connector

							DSND		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors		
ΔX					ANGLAR	±5°		DWN	VIEW: 	PART NO.: X2011WRS-07A-9TSN		
ΔX					L≤ 4	±0.2		CHKD	UNIT: mm/in	DWG NO.: X-X2011WRS-07A-9TSN		
ΔX					4<L≤ 16	±0.3		APPD	SIZE: A4			
ΔX					16<L≤ 63	±0.4						
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5						
REVISIONS							UNSPECIFIED TOLERANCES			WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-da.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED				1/1	A0