


PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 300V AC/minute

耐受电压: 300V AC/分钟

Temperature range: -40°C ~ +105°C

温度范围: -40°C ~ +105°C

Insulation resistance: ≥ 500MΩ

绝缘电阻: ≥ 500MΩ

Contact resistance: ≤ 20mΩ

接触电阻: ≤ 20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U" Gold

镀层: 1U" Gold

Wave soldering temperature: 255 ± 5°C, 10S

波峰焊温度: 255 ± 5°C, 10S

X1311 F R - 06 - C43 D24

① ② ③ ④ ⑤ ⑥

1. Series No

2. Category: F-Female

3. Welding Board Angle: R-Straight 90°

4. Row No. Pin No: XX-01~40 Pin

5. Plastic height: C=4.3mm

6. Pin Length: D=2.4mm

X1311FR-06-C43D24	PA6T	Brass	X1311W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.27mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X1311FR-06-C43D24
APPD	SIZE: A4	DWG NO.: X-X1311FR-06-C43D24
		WEIGHT
		SHEET 1/1
		REVISION A0