





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 葦






TYPE A



TYPE B




TYPE C



PART NO.: X332A H-28 -PB XX
① ② ③ ④ ⑤ ⑥

- 1.Series No:332A-TYPE A
332B-TYPE B
332C-TYPE C
2.Category:H-Housing
3.Row No.Pin No:XX-See Table A
4.Morphology:Blank-No CPA Feature
C-With CPA Feature
5.Material:PB-PBT
6.Color:Blank-Black; GR-Gray;
BL-Blue

规格Specifications:
额定电压Voltage rating:60V AC/DC
额定电流Current rating:3A AC/DC
耐受电压Withstanding voltage:500V AC/minute
温度范围Temperature range:-40℃~+125℃
绝缘电阻Insulation resistance:≥100MΩ
接触电阻Contact resistance:≤10mΩ (测试后≤30mΩ)



X332CH-XXC-PBXX	X332CWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332BH-XXC-PBXX	X332BWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332AH-XXC-PBXX	X332AWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332CH-XX-PBXX	X332CWRS-XX	X332XT-BSN	PBT UL94 V-0
X332BH-XX-PBXX	X332BWRS-XX	X332XT-BSN	PBT UL94 V-0
X332AH-XX-PBXX	X332AWRS-XX	X332XT-BSN	PBT UL94 V-0
PART NO.	Suitable XKB WAFER	Suitable XKB Terminal	MATERIAL

TABLE A

PIN NO.	A	B	C	D
8	10.00		6.00	15.60
12	14.00	15.90	10.00	19.60
16	18.00	19.90	14.00	23.60
20	22.00	23.90	18.00	27.60
24	26.00	27.90	22.00	31.60
28	30.00	31.90	26.00	35.60
32	34.00	35.90	30.00	39.60
40	42.00	43.90	38.00	47.60

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	





DESIGN	桑 葦	VIEW:	MODEL TYPE: 2.0mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X332AH-28-PB
APPROVED		SIZE: A4	DWG NO.: X-X332AH-28-PB

XKB INDUSTRIAL PRECISION CO.,LIMITED






SCALE	PAGE	REVISION
N/A	1/3	A0

NO CPA FEATURE


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 葚



MATED DIMENSION



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE: 2.0mm Crimp Style Housing		
PART NO.: X332AH-28-PB		
DWG NO.: X-X332AH-28-PB		

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	2/3	A0

1


2

3




4

WITH CPA FEATURE


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 葚



MATED DIMENSION



16~40 PIN



16~40 PIN

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚	VIEW:	MODEL TYPE: 2.0mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X332AH-28-PB
APPROVED		SIZE: A4	DWG NO.: X-X332AH-28-PB

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	3/3	A0

1

2

3

4