



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.05.16	阿树
/	N/A		升级整理图面	/	/



■SPECIFICATIONS



- Voltage rating:250V AC/DC
 - Current rating:2A AC/DC
 - Withstanding Voltage:1000V AC/minute
 - Temperature range:-40°C~+105°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤20mΩ
- Material:
Rubber core: PA46 UL94V-0
Contact PIN: Gold-plated 1U"

PART NO.:

X2011 W R-04 A-46 V01
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:XX-02~16Pin
⑤Plug the Pin&Special NO:
A-With Located Block
⑥Material:PA46 UL94V-0
⑦Planting: V01-Gold-plated 1U"

Poles	DIM.A	DIM.B
2P	2.0	6.0
3P	4.0	8.0
4P	6.0	10.0
5P	8.0	12.0
6P	10.0	14.0
7P	12.0	16.0
8P	14.0	18.0
9P	16.0	20.0
10P	18.0	22.0
11P	20.0	24.0
12P	22.0	26.0
13P	24.0	28.0
14P	26.0	30.0
15P	28.0	32.0
16P	30.0	34.0



X2011WR-04A-NOSNB	PA46 UL 94V-0	Gold-plated 1U"	Tin-plated	2011H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X2011WR-04A-NOSNB
APPROVED		SIZE: A4	DWG NO.: