


PCB LAYOUT

Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压: 300V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:≥500MΩ
绝缘电阻: ≥500MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ
Material:PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category:1U"Gold
镀层: 1U"Gold
Wave soldering temperature:255±5℃, 10S
波峰焊温度: 255±5℃, 10S

X1311 F R - 07 - C43 D24
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:R-Straight 90°
- 4.Row No.Pin No:XX-01~40 Pin
- 5.Plastic height:C=4.3mm
- 6.Pin Length:D=2.4mm

X1311FR-07-C43D24	PA6T	Brass	X1311W
PART N0	Material	Material(Pin)	Suitable XKB Wafer

					ANGLAR	±5°	
ΔX					L≤ 4	±0.2	
ΔX					4<L≤ 16	±0.3	
ΔX					16<L≤ 63	±0.4	
MARK	DESCRIPTION		DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn							



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN		VIEW:	PART NO.: X1311FR-07-C43D24
CHKD		UNIT: mm/in	DWG NO.: X-X1311FR-07-C43D24
APPD		SIZE: A4	
		WEIGHT	SHEET 1/1
			REVISION A0