



Specifications.

- Voltage rating: 250V AC/DC
- Current rating: 7A AC/DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C ~ +85°C
- Insulation resistance: 1000mΩ Min
- Contact resistance: 20mΩ Max
- Material: Nylon66 UL94V-0

X8475 W V -03- N0 SN
① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Wedging Board Angle : V-Straight 180°
- ④ Row No. Pin No. XX-02-08
- ⑤ Material: N0-Nylon UL94V-0
- ⑥ Planting Category: SN-Bright Tin plating

Poles	Dimensions (mm)	
	A	B
2	7.50	15.20
3	12.50	20.20
4	17.50	25.20
5	22.50	30.20
6	27.50	35.20
7	32.50	40.20
8	37.50	45.20

X8475WV-03-N0SN	Nylon66 UL 94V-0	Brass	Tin-Plated	X8475H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

DSND		SCALE: N/A	MODEL TYPE: 7.50mm Crimp Style Connectors		
DWN		VIEW:	PART NO.: X847WV-03-N0SN		
CHKD		UNIT: mm/in	DWG NO.: X-X8475WV-03-N0SN		
APPD		SIZE: A4			
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET 1/1	REVISION A0