







Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:20A AC/DC

额定电流: 20A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

K 838100 H F - 02 - N2
① ② ③ ④ ⑤ ⑥

1.K: XKBTEK-Car Connector

2.XKB Series No

3.Category:H-Housing

4.Special No:F-Female Housing

5.Row No.Pin No:XX-01~04 Pin

6.Material:N2-PA66 UL94V-2

Poles	Dimensions(mm)	
	A	B
01	/	9.30
02	8.38	17.68
03	16.76	26.06
04	25.14	34.44

K838100HF-02-N2	PA66	K838100HF	K838100HF
PART NO	Material	Suitable XKB Housing	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 8.38mm Automobile connector
DWN		VIEW:	PART NO.: K838100HF-02-N2
CHKD		UNIT: mm/in	DWG NO.: X-K838100HF-02-N2
APPD		SIZE: A4	
			WEIGHT
			SHEET
			REVISION
			1/1
			A0

					ANGULAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION					DATE	REVISED
REVISIONS					APPROVED	UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED