




Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:7A AC/DC

额定电流: 7A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25°C-+85°C




温度范围: -25°C ~ $+85^{\circ}\text{C}$

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max


接触电阻: 20mΩ Max



PCB Layout




02 Pin



03 Pin



04 Pin



05 Pin



06 Pin

Circuit size Layout

X9357 W R - 04 - N2 SN
 (1) (2) (3) (4) (5) (6)

1.Series No

2. Category: W-Wafer

3. Welding Board Angle: R-Straight 90°

4.Row No.Pin No:XX-02~06P

5. Material: N0-PA66 UL94V-0 ;

N2-PA66 UL94V-2

Poles	Dimensions(mm)	
	A	B
02	4.20	9.80
03	8.40	14.00
04	12.60	18.20
05	16.80	22.40
06	21.00	26.60

X9357WR-04-N2SN	PA66	Brass	X9357HM
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dq.cn

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 4.2mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X9357WR-04-N2SN		
CHKD		UNIT: mm/in	DWG NO.: X-X9357WR-04-N2SN		
APPD		SIZE: A4			
L. PRECISION CO., LIMITED			WEIGHT	SHEET 1/1	REVISION A0