





Recommended P.C.B Layout
General Tolerance±0.05

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤20mΩ
- After environmental testing : ≤30mΩ

X2012 W V-09- N0 SN
① ② ③ ④ ⑤ ⑥

- ① Series No.
② Category : W-WAFER
③ Wedding Board Angle : V-Stright 180°
④ Row No.-Pin No.: XX-02P~16P
⑤ Material : N0-PA66 94V-0
⑥ Plating Category: Sn-Bright Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	5.20	10	18.00	22.00	21.20
03	4.00	8.00	7.20	11	20.00	24.00	23.20
04	6.00	10.00	9.20	12	22.00	26.00	25.20
05	8.00	12.00	11.20	13	24.00	28.00	27.20
06	10.0	14.00	13.20	14	26.00	30.00	29.20
07	12.0	16.00	15.20	15	28.00	32.00	31.20
08	14.0	18.00	17.20				
09	16.0	20.00	19.20				

X2012WV-09-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X2012H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors		
Δx					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X2012WV-09-N0SN		
Δx					4<L≤16	±0.3	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2012WV-09-N0SN		
Δx					16<L≤63	±0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION				DATE	REVISED						APPROVED	L>63	±0.5
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														
												WEIGHT	SHEET	REVISION
												1.0g	1/1	A0