


APART NO.:

①Series Name:X10C25=1.00mm Pitch(H:2.50mm)

②Number of terminals:XX=02-35PIN

③Plating : G:Gold Flash Over Nickel

T: Tin Over Nickel

④Z:positive needle F:negative needle

3.PERFORMANCE:

3.1: CURRENT RATING:0.5A/PIN

3.2: VOLTAGE RATING:50V(AC/DC)

3.3: CONTACT RESISTANCE: INITIAL VALUE

3.4:INSULATION RESISTANCE:500MOHM Min.

3.5:DIELERIC WITHSTANDING VOLTAGE:250V AC FOR 1MINUTE

3.6:DURABILT: 20 TIMES Min

3.7:OPERATING TEMPERATURE:-40°C~+85°C
OPERATING HUMIDITY RANGE:20% TO 95%

CD

DESIGN	阿树	VIEW: 	MODEL TYPE: FPC CONNECTOR
CHECKED		UNIT: mm/in	PART NO.: X10C2520GZ
APPROVED		SIZE: A4	DWG NO.: X10C2520GZ

SCALE	PAGE	REVISIO
N/A	1/1	A1