



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.19	桑葚
A1	N/A		图面升级整理图面	2025.10.20	阿树

PART NO.:

X1501 H-2x11-NO
① ② ③ ④

- ①Series No
②Category:H—Housing
③Row No.Pin No:2xXX~2x05~2x15Pin
④Material:N0—PA66,UL 94V-0,WHITE

Specifications(规格):

- 1.Voltage rating(额定电压):100V AC DC
- 2.Current rating(额定电流):2.0A AC/DC
- 3.Withstanding voltage(耐压值): $\geq 500V$ AC/minute
- 4.Insulation resistance(绝缘电阻):500MΩ Min
- 5.Contact resistance(接触电阻):20mΩ Max
- 6.Temperature range(使用温度):-25℃~+85℃

Poles	Dimensions(mm)			
	A	B	C	D
2x05	7.50	6.00	11.20	9.30
2x06	9.00	7.50	12.70	10.80
2x07	10.50	9.00	14.20	12.30
2x08	12.00	10.50	15.70	13.80
2x09	13.50	12.00	17.20	15.30
2x10	15.00	13.50	18.70	16.80
2x11	16.50	15.00	20.20	18.30
2x12	18.00	16.50	21.70	19.80
2x13	19.50	18.00	23.20	21.30
2x15	22.50	21.00	26.20	24.30

X1501H-2x11-N0	PA66 94V-0	X1501W	X1501T
PART NO.	MATERIAL	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAuCES

XKIB 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 1.5mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X1501H-2x11-N0
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1