

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.12.23	阿树

- SPECIFICATIONS
- Voltage rating:50V AC,DC
 - Current rating:1A,AC,DC
 - Withstanding Voltage:500V AC/minute
 - Insulation resistance:100MQ min
 - Temperature range:-45°C+95°C
 - Contact resistance:20mΩ max

PART NO.:
X1010 W V S-08-LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-02~15Pin
⑥Material:LP-LCP UL94V-0
⑦Planting: SN-Tin-Plated
V01-Gold Flsh

PART NO.	Dimensions (mm)	
	A	B
02	2.00	5.00
03	2.00	5.00
04	3.00	6.00
05	4.00	7.00
06	5.00	8.00
07	6.00	9.00
08	7.00	10.00
09	8.00	11.00
10	9.00	12.00
11	10.00	13.00
12	11.00	14.00
13	12.00	15.00
14	13.00	16.00
15	14.00	17.00

X1010WVS-08-LPSN	LCP	Brass	X1010H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	1.0mm Crimp Style Housing
PART NO.:	X1010WVS-08-LPSN
DWG NO.:	

SCALE	PAGE	REVISION
N/A	1/1	A1

