



REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A		图框升级整理图面	2024.08.03







Specifications:
规格:
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:7A AC/DC
额定电流: 7A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-45℃~+1255℃
温度范围: -45℃~+1255℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤10mΩ
After environmental testing:≤20兆欧
环境测试后: ≤20兆欧

PART NO.:
X9357 H M-2x02 B-N0 XX
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
② Category:H-HSG
③ Welding Board Angle:M-Male HGS
④ Row No.-Pin No.:2xXX-2x04P~2x36P
⑤ Plug the Pin & special No:B-With the back seat
⑥ Material:N0-PA66 94V-0
⑦ Color:Blank-Natural Color

Poles	Dimensions(mm)				
	A	B	C	D	E
4	4.20	40.20	29.20	17.60	12.90
6	8.40	44.40	33.40	21.80	17.10
8	12.60	48.60	37.60	26.00	21.30
10	16.80	52.80	41.80	30.20	25.50
12	21.00	57.00	46.00	34.40	29.70
14	25.20	61.20	50.20	38.60	33.90
16	29.40	65.40	54.40	42.80	38.10
18	33.60	69.60	58.60	47.00	42.30
20	37.80	73.80	62.80	51.20	46.50
22	42.00	78.00	67.00	55.40	50.70
24	46.20	82.20	71.20	59.60	54.90
36	71.40	107.40	96.40	81.50	76.78



X9357HM-2x02B-N0	Nylon 66 94V-0	X9357TF	X9357HF-B
PART NO	Material	Suitable XBK Terminal	Suitable XBK Terminal
DESIGN	阿 树	VIEW:	MODEL TYPE: 4.20mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9357HM-2x02B-N0
APPROVED		SIZE: A4	DWG NO.: X-X9357HM-2x02B-N0
UNSPECIFIED TOLERANCES		SCALE	PAGE
		N/A	1/1
		REVISION	A1

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED