






D		E		F	
REV.	EC#	DESCRIPTION	DATE DRAWN	CHECK	APPROVED
1.00		初版发行	2020-8-28		

15P	40	38.6	35
14P	37.5	36.1	32.5
13P	35	33.6	30
12P	32.5	31.1	27.5
11P	30	28.6	25
10P	27.5	26.1	22.5
9P	25	23.6	20
8P	22.5	21.1	17.5
7P	20	18.6	15
6P	17.5	16.1	12.5
5P	15	13.6	10
4P	12.5	11.1	7.5
3P	10	8.6	5
2P	7.5	6.1	2.5
NUMBER OF PINS	DIM.A	DIM.B	DIM.C



PCB LAYOUT

2PIN

适用基板厚度: 1.6mm

温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$

额定电压: 250V AC/DC

额定电流: 3A

接触电阻: $\leq 0.02\Omega$

绝缘电阻: $\geq 1000\text{M}\Omega$

耐 压: 1000V AC/minute

- 技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

2	PIN	n PCS	材质:黄铜,电镀:镀亮锡
1	Housing	1 PCS	材质:PA66 (UL94V-0),颜色:白色
NO.	NAME	Q'TY	DESCRIPTION



深圳市韩下电子有限公司

DRAW :	黄彬	2020-8-28	TITLE: 针座		DRAW NAME:		
DESIGN:					HX-XH2. 54-5PWZ-WG		
CHECK:	张伟	2020-8-28	SERIES: XH2.5 SERIES		DRAW NO.		
APPROVED	罗小春	2020-8-28	P/N:		UNIT:	SHEET:	
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	mm	1/1	

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°.	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	



深圳市韩下电子有限公司
Shenzhen Hanxia Electronic Co., Ltd
Tel: 0755-23086569

承 认 书

SPECIFICATION FOR APPROVAL

产 品 编 码
Material code:

产品名称 Project:

针座

规格型号 Part No:

HX-XH2. 54-5PWZ-WG

贵公司承认印 Approval signatures

料 号/Part No.	签 章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	