




Recommended PCB Layout (Top view)
Tolerance: $\pm 0.05\text{mm}$

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 2A AC/DC

额定电流: 2A AC/DC

Withstanding voltage: 1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range: -25°C ~ $+105^{\circ}\text{C}$

温度范围: -25°C ~ $+105^{\circ}\text{C}$

Insulation resistance: $\geq 1000\text{M}\Omega$

绝缘电阻: $\geq 1000\text{M}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

接触电阻: $\leq 20\text{m}\Omega$

X2016 W V - 02 R - LP SN
① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: V-Stright 180°
4. Row No. Pin No: XX-02~16Pin
5. Special No: R-DIP 2.2mm
6. Material: LP-LCP UL94V-0, Natural
7. Plating: SN- Tin Plated

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	2.00	4.90	6.00	10	18.00	20.90	22.00
03	4.00	6.90	8.00	11	20.00	22.90	24.00
04	6.00	8.90	10.00	12	22.00	24.90	26.00
05	8.00	10.90	12.00	13	24.00	26.90	28.00
06	10.00	12.90	14.00	14	26.00	28.90	30.00
07	12.00	14.90	16.00	15	28.00	30.90	32.00
08	14.00	16.90	18.00	16	30.00	32.90	34.00
09	16.00	18.90	20.00				

X2016WV-02R-LPSN	LCP	Brass	X2016H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2016WV-02R-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X2016WV-02R-LPSN
APPD		SIZE: A4	

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0