

1



2

3

4

## REVISIONS

| REV. | ECN NO. | LOCATION | DESCRIPTION | DATE       | DESIGN |
|------|---------|----------|-------------|------------|--------|
| A1   | N/A     |          | 图框升级整理图面    | 2024.08.03 | 阿 树    |






## ■SPECIFICATIONS

- Voltage rating:600V AC/DC
- Current rating:7A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:

X9357 W R-2x12 ES-N2 SN  
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category:W-Wafer
- ③ Welding Board angle:R-Stright 90°
- ④ Row No.Pin No:2xXX-2x01P~2x12P
- ⑤ Plug the Pin&Specal NO.:  
ES-With Ears and Screw Holes
- ⑥ Material:N2-PA66 94V-2
- ⑦ Plating:SN-Bright tin plating



| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 2x01  |                | 5.40  | 2x07  | 25.20          | 30.60 |
| 2x02  | 4.20           | 9.60  | 2x08  | 29.40          | 34.80 |
| 2x03  | 8.40           | 13.80 | 2x09  | 33.60          | 39.00 |
| 2x04  | 12.60          | 18.00 | 2x10  | 37.80          | 43.20 |
| 2x05  | 16.80          | 22.20 | 2x11  | 42.00          | 47.40 |
| 2x06  | 21.00          | 26.40 | 2x12  | 46.20          | 51.60 |

|                     |                   |               |             |                      |
|---------------------|-------------------|---------------|-------------|----------------------|
| X9357WR-2x12ES-N2SN | Nylon 66 UL 94V-2 | Brass         | Tin-Plated  | X9357H               |
| PART NO             | Material          | Material(Pin) | Finish(Pin) | Suitable XKB Housing |

|                        |       |
|------------------------|-------|
| ANGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|                        |     |             |                                                                                       |                                              |
|------------------------|-----|-------------|---------------------------------------------------------------------------------------|----------------------------------------------|
| DESIGN                 | 阿 树 | VIEW:       |  | MODEL TYPE:<br>4.20 mm Crimp Style Connector |
| CHECKED                |     | UNIT: mm/in |                                                                                       | PART NO.:<br>X9357WR-2x12ES-N2SN             |
| APPROVED               |     | SIZE: A4    |                                                                                       | DWG NO.:<br>X-X9357WR-2x12ES-N2SN            |
| DESIGNER: CO., LIMITED |     | SCALE       | PAGE                                                                                  | REVISION                                     |
|                        |     | N/A         | 1/1                                                                                   | A1                                           |

1

2

3

4