

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.22	阿树

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:300V AC/minute

耐受电压: 300V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Wave soldering temperature:255±5℃, 10S

波峰焊温度: 255±5℃, 10S

PART NO.:

X1321 W R-2x15 J-C40 D18
① ② ③ ④ ⑤ ⑥ ⑦

①Series No

②Category:W-Wafer

③Welding Board Angle:R-Stright 90°





④Row No.Pin No:2xXX-2x01~2x40P

⑤Plastic Height:J=1.0mm

⑥Pin Length:C=4.0mm

⑦Pin Length:D=1.8mm

X1321WR-2x15J-C40D18		PA6T	Brass	X1321F
PART NO		Material	Material(Pin)	Suitable XKB Female
DESIGN	阿树	VIEW: 	MODEL TYPE: 1.27mm BTB Connector	
CHECKED		UNIT: mm/in	PART NO.: X1321WR-2x15J-C40D18	
APPROVED		SIZE: A4	DWG NO.: X-X1321WR-2x15J-C40D18	
		SCALE	PAGE	REVISION
		N/A	1/1	A1



P.C.B LAYOUT

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED