



P.C.B LAYOUT



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:300V AC/minute

耐受电压: 300V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Reflow soldring temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S

X1321 W V S - 2x12 J - C40 D53
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Strighr 180°

4.Welding Way:S-SMT

5.Row No.Pin No:2xXX-2x01~2x40Pin

6.Plastic Height:J=1.0mm

7.Pin Length:C=4.0mm

8.Pin Length:D=5.3mm

Poles	A(mm)
2x02~2x15	0.10
2x16~2x30	0.15
2x31~2x40	0.20
2x41~2x50	0.25

X1321WVS-2x12J-C40D53	PA6T	Brass	X1321F
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN	VIEW:	PART NO.: X1321WVS-2x12J-C40D53
CHKD	UNIT: mm/in	DWG NO.: X-X1321WVS-2x12J-C40D53
APPD	SIZE: A4	WEIGHT
		SHEET 1/1
		REVISION A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED