




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.25	阿树



Technical Notes

1.It shows that it is smooth and clean, and there are no obvious shrinkage pits and weld marks



2.Current rating:14A AC/DC

3.Temperature range:-40℃-+125℃

PART NO.:

K 282103 H M-02-N0
① ② ③ ④ ⑤ ⑥

①K:XKBTEK-Car Connector
②XKB Series No
③Category:H-Housing
④Special No:M-Male Housing
⑤Row No.Pin No:02 Pin
⑥Material:N0-PA66 UL94V-0



K282103HM-XX-N0	PA66	K282103HF	K282103TF
PART NO	Material	Suitable XKB Female	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	6.0mm Automobile connector
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4
PART NO.: K282103HM-02-N0			
DWG NO.:			