






R1



R2



PCB LAYOUT (R1)



PCB LAYOUT (R2)

Specifications:
 规格:
 Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage: 300V AC/minute
 耐受电压: 300V AC/分钟
 Temperature range: -40°C ~ +105°C
 温度范围: -40°C ~ +105°C
 Insulation resistance: ≥ 500MΩ
 绝缘电阻: ≥ 500MΩ
 Contact resistance: ≤ 20mΩ
 接触电阻: ≤ 20mΩ
 Material: PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category: 1U"Gold
 镀层: 1U"Gold
 Reflow soldering temperature: 260±5°C, 10S
 回流焊温度: 260±5°C, 10S

X1311 F V S - 25 - C43 D35 R1
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No
2. Category: F-Female
3. Welding Board Angle: V-Straight 180°
4. Welding Way: S-SMT
5. Row No. Pin No: XX-01~40Pin
6. Plastic Height: C=4.3mm
7. Pin pitch: D=3.5mm
8. Type: R1 ; R2

X1311FVS-25-C43D35R1	PA6T	Brass	X1311W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	1.27mm BTB Connector
CHKD		UNIT: mm/in	PART NO.:
APPD		SIZE: A4	X1311FVS-25-C43D35R1
			DWG NO.:
			X-X1311FVS-25-C43D35R1
		WEIGHT	SHEET
		1/1	REVISION
			A0

XKB INDUSTRIAL PRECISION CO., LIMITED