





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2024.09.03	阿树
A2	N/A		产品图面更新	2026.01.14	阿树



PART NO.:

X1255 H-20 A-N0 XX
① ② ③ ④ ⑤ ⑥

- ①Series No
②Category:H-HSG
③Row No.Pin No:XX-02~20Pin
④Plug the Pin & Special N0:A-Double Salient
⑤Material:N0-PA66 UL94V-0
⑥Whether containing halogen:HF-Halogen free

Poles	Dimensuons(mm)			Poles	Dimensuons(mm)		
	A	B	C		A	B	C
02	1.25	3.85	6.10	12	13.75	16.35	18.60
03	2.50	5.10	7.35	13	15.00	17.60	19.85
04	3.75	6.35	8.60	14	16.25	18.85	21.10
05	5.00	7.60	9.85	15	17.50	20.10	22.35
06	6.25	8.85	11.10	16	18.75	21.35	23.60
07	7.50	10.10	12.35	17	20.00	22.60	24.85
08	8.75	11.35	13.60	18	21.25	23.85	26.10
09	10.00	12.60	14.85	19	22.50	25.10	27.35
10	11.25	13.85	16.10	20	23.75	26.35	28.60
11	12.50	15.10	17.35				

X1255H-20A-N0HF	PA66 UL 94V-0 Halogen Free	X1255T	X1255W
X1255H-20A-N0	PA66 UL 94V-0		
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 1.25mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X1255H-20A-N0
APPROVED		SIZE:	A4	DWG NO.: X-X1255H-20A-N0