


Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥100MΩ

绝缘电阻: ≥100MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ


After environmental testing:≤30mΩ

环境测试后: ≤30兆欧


X1102 W R S-2x08 -N0V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No.
- 2.Category:W-wafer
- 3.Welding Board Angle:R-Right Angle 90°
- 4.Welding Way:S-SMT
- 5.Row No-Pin No: 2xXX-2x03P~2x25P
- 6.Plug the pin&special No
- 7.Material:46-PA46 94V-0 N0-PA66-94V-0
- 8.Planting Category:V01-All Gold Flash
- 9.Color: Blank-natural color



Recommended PCB Layout
General Tolerance±0.05



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2x03	2.00	5.60	4.20	2x12	11.00	14.60	13.20
2x04	3.00	6.60	5.20	2x13	12.00	15.60	14.20
2x05	4.00	7.60	6.20	2x14	13.00	16.60	15.20
2x06	5.00	8.60	7.20	2x15	14.00	17.60	16.20
2x07	6.00	9.60	8.20	2x16	15.00	18.60	17.20
2x08	7.00	10.60	9.20	2x17	16.00	19.60	18.20
2x09	8.00	11.60	10.20	2x18	17.00	20.60	19.20
2x10	9.00	12.60	11.20	2x20	19.00	22.60	21.20
2x11	10.00	13.60	12.20	2x25	24.00	27.60	26.20

X1102WRS-2x08-46V01	Nylon 46 UL 94V-0	Brass	Tin-Plated	X1102T
X1102WRS-2x08-N0V01	Nylon 66 UL 94V-0		Gold Flash	
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

Wire to board connector

						DSND		DATE		SCALE: N/A	MODEL TYPE: 1.00mm Crimp Style Connectors		
Δx					units: mm	DWN		DATE		VIEW: 	PART NO.:		
Δx					X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	X1102WRS-2x08-N0V01		
Δx					X.XX ±0.1mm			DATE		SIZE: A4	DWG NO.:		
MARK	DESCRIPTION				DATE	REVISED	APPROVED			X.XXX ±0.05mm	X-X1102WRS-2x08-N0V01		
REVISIONS						UNSPECIFIED TOLERANCES					WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											XKB INDUSTRIAL PRECISION CO.,LIMITED		