



Technical drawing of a mechanical part with dimensions:

- Overall width: $B \pm 0.20$
- Overall height: $1.00 [0.039]$
- Height of the main body: $6.40 [0.252]$
- Feature: A triangular symbol (likely a chamfer or fillet indicator) is shown on the right side of the main body.



AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

X2026 W V S-2x03 S-9T SN XX
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- | poles | Dimensions(mm) | | | poles | Dimensions(mm) | | | Poles | Dimensions(mm) | | |
|-------|----------------|-------|-------|-------|----------------|-------|-------|-------|----------------|-------|-------|
| | A | B | C | | A | B | C | | A | B | C |
| 2x02 | 2.00 | 6.00 | 4.00 | 2x09 | 16.00 | 20.00 | 18.00 | 2x16 | 30.00 | 34.00 | 32.00 |
| 2x03 | 4.00 | 8.00 | 6.00 | 2x10 | 18.00 | 22.00 | 20.00 | 2x17 | 32.00 | 36.00 | 34.00 |
| 2x04 | 6.00 | 10.00 | 8.00 | 2x11 | 20.00 | 24.00 | 22.00 | 2x18 | 34.00 | 38.00 | 36.00 |
| 2x05 | 8.00 | 12.00 | 10.00 | 2x12 | 22.00 | 26.00 | 24.00 | 2x19 | 36.00 | 40.00 | 38.00 |
| 2x06 | 10.00 | 14.00 | 12.00 | 2x13 | 24.00 | 28.00 | 26.00 | | | | |
| 2x07 | 12.00 | 16.00 | 14.00 | 2x14 | 26.00 | 30.00 | 28.00 | | | | |
| 2x08 | 14.00 | 18.00 | 16.00 | 2x15 | 28.00 | 32.00 | 30.00 | | | | |

DESIGN	阿树	VIEW: 	MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X2026WVS-2x03-9TSN
APPROVED		SIZE: A4	DWG NO.:

XK13 星城
Connection

SCALE	PAGE	REVISION
N/A	1/1	A1